

## Product data sheet

### Characteristics

# 3045VH-VW

## Gridplate and Skin, Clipsal Iconic, 5 Gang, Vertical/Horizontal

### Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20

### Complementary

Range compatibility	Clipsal Iconic switch
Product destination	Switch
Device mounting	Flush
Number of rocker	5
Device composition	Fixing frame
Installation direction	Horizontal/vertical
Fixing mode	Screw
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): grid plate PP (polypropylene): flaps POM (polyoxymethylene): locking bar PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	7.5 mm
Embedding depth	15 mm
Net weight	0.04 kg

### Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.8 cm
Package 1 Length	12 cm
Package 1 Weight	60 g
Unit Type of Package 2	BB1

Number of Units in Package 2	15
Package 2 Height	1 cm
Package 2 Width	12.5 cm
Package 2 Length	21 cm
Package 2 Weight	900 g

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1