

## Product data sheet

### Characteristics

## 3046C-WY

Clipsal Iconic, Switch Plate Skin, 6 Gang,  
Horizontal/Vertical Mount



### Main

Range	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Cover frame
Colour tint	Warm grey (WY)
Type of packing	Polybag
Quantity per set	Set of 20

### Complementary

Range compatibility	Clipsal Iconic switch
Product destination	Switch
Device mounting	Flush
Number of rocker	6
Installation direction	Horizontal/vertical
Fixing mode	Clip-on
Surface finish	Matt
Surface treatment	Untreated
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin
Height	120 mm
Width	78 mm
Depth	9 mm
Net weight	0.02 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.946 cm
Package 1 Width	8.33 cm
Package 1 Length	12.479 cm
Package 1 Weight	25 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	32.8 cm
Package 2 Width	10.6 cm

Package 2 Length	14.6 cm
Package 2 Weight	655.4 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	33.5 cm
Package 3 Width	26.1 cm
Package 3 Length	33.5 cm
Package 3 Weight	3.662 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations