

Product data sheet

Characteristics

30BD1M-WE

SWITCH MECH 1/2W 10A BED1



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-pole
Actuator	Rocker
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	Clip-in
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	BED1
Marking location	Marking on surface

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	13.8 g
Package 1 Height	30 mm
Package 1 width	23 mm
Package 1 Length	23 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.15 kg
Package 2 Height	39 mm
Package 2 width	55 mm
Package 2 Length	115 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	7.5 kg
Package 3 Height	237 mm
Package 3 width	203 mm
Package 3 Length	300 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile