

Product data sheet

Characteristics

30BDM-WE

SWITCH MECH 1/2W 10A BED



Main

| | |
|---------------------|------------------------------|
| Range of product | Standard Series Series 30 |
| Product brand | Clipsal |
| Device presentation | Basic element |

Complementary

| | |
|--------------------------------|--------------------|
| Switch function | 1-pole |
| Number of rocker | 1 |
| Number of poles | 1 |
| Device mounting | Flush |
| Fixing mode | Clip-in |
| Surface finish | Glossy |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 10 A |
| Marking | BED |
| Marking location | Marking on surface |
| Actuator | Rocker |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 14.0 g |
| Package 1 Height | 2.5 cm |
| Package 1 width | 2.5 cm |
| Package 1 Length | 3.2 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 152.0 g |
| Package 2 Height | 4.2 cm |
| Package 2 width | 5.6 cm |
| Package 2 Length | 11.6 cm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 500 |
| Package 3 Weight | 9.0 kg |
| Package 3 Height | 23.7 cm |
| Package 3 width | 20.3 cm |
| Package 3 Length | 30 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |