

Product data sheet

Characteristics

30D-WE

Flush Switch, 1 Gang, 2 Pole, 250VAC, 10A,
Architrave



Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	2-pole
Number of rocker	1
Number of poles	2
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	3 cm
Package 1 Length	7.5 cm
Package 1 Weight	31 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	10
Package 2 Height	7.8 cm
Package 2 Width	8.8 cm
Package 2 Length	17 cm
Package 2 Weight	372 g
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	23.8 cm
Package 3 Width	34.2 cm
Package 3 Length	39 cm
Package 3 Weight	10 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile