

Product data sheet

Characteristics

30FM-WE

SWITCH MECH 1/2W 10A FAN



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	Clip-in
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Fan
Marking location	Marking on surface
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.0 g
Package 1 Height	2.3 cm
Package 1 width	2.2 cm
Package 1 Length	2.7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile