

Product data sheet

Characteristics

30M-WE

Clipsal - Mechanisms, Switch Mechanisms, 30 Series, 250V 10A - 1 Way / 2 Way



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Material	PVC (polyvinyl chloride)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	0.014 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.7 cm
Package 2 Width	5.1 cm
Package 2 Length	11.5 cm
Package 2 Weight	0.15 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Height	23.7 cm
Package 3 Width	20.3 cm

Package 3 Length	30 cm
Package 3 Weight	7.76 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile