

Product data sheet

Characteristics

30M35-STOVE-WE

30M35 MARKED STOVE



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Number of rocker	1
Device mounting	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	35 A
Marking	Stove
Marking location	Marking on surface
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.5 g
Package 1 Height	2.36 cm
Package 1 width	2.36 cm
Package 1 Length	2.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.093 kg
Package 2 Height	3.4 cm
Package 2 width	5.2 cm
Package 2 Length	7.3 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	0.988 kg
Package 3 Height	10.2 cm
Package 3 width	12 cm
Package 3 Length	17 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile