

## Product data sheet

### Characteristics

# 30M35OV-WE

Clipsal - Mechanisms, Switch Mechanisms, 30 Series, 35A Mechanisms - Marked, OVEN



#### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element



#### Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	35 A
Marking	Oven
Marking location	Marking on surface
Mounting Type	Clip-in
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	16.5 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

