

Product data sheet

Characteristics

30M35R-WE

Switch Mechanisms, 30 Series, 35A

Mechanisms, Marked RANGE



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	Clip-in
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	35 A
Marking	Range
Marking location	Marking on surface
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	16.5 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	3.4 cm
Package 2 Width	5.2 cm
Package 2 Length	7.3 cm
Package 2 Weight	0.093 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	10.2 cm
Package 3 Width	12 cm

Package 3 Length	17 cm
Package 3 Weight	0.988 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile