

Product data sheet

Characteristics

30MAM15-WE

SWITCH MECHANISM 1 WAY / 2 WAY

MANUAL / AUTO



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	1-way 2-way
Number of rocker	1
Number of poles	2
Device mounting	Flush
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	35 A
Marking	AUTO-MAN
Marking location	Marking on surface
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.014 kg
Package 1 Height	2.36 cm
Package 1 width	2.36 cm
Package 1 Length	2.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.078 kg
Package 2 Height	3.4 cm
Package 2 width	5.2 cm
Package 2 Length	7.3 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	8.046 kg
Package 3 Height	22.6 cm
Package 3 width	19.1 cm
Package 3 Length	35.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile