

Product data sheet

Characteristics

30MBP-WE

Clipsal - Mechanisms, Switch Mechanism, 250V, 15A



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element
Control button type	Push-button

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	15 A
Marking	Without marking
Actuator	Push-button

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	3.16 cm
Package 1 Weight	16.191 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.