

Product data sheet

Characteristics

30MBPN-WE

Clipsal - Mechanisms, Switch Mechanism, 250V, 15A Neon



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element
Control button type	Push-button




Complementary

Installation Type	Flush
Local signalling	neon
[Ue] rated operational voltage	250 V AC
Rated current	15 A
Marking	Without marking
Mounting Type	Clip-in
Actuator	Push-button

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	3.16 cm
Package 1 Weight	16.438 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.