

Product data sheet

Characteristics

30MBPN12-WE

SWITCH MECHANISM ILLUMINATED BELL PRESS 12V



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element
Control button type	Push-button



Complementary

Actuator	Push-button
Device mounting	Flush
Fixing mode	Clip-in
Local signalling	neon
[Ue] rated operational voltage	12 V DC
Rated current	15 A
Marking	Without marking

Packing Units

Package 1 Weight	0.018 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.