

## Product data sheet

### Characteristics

# 30MOS-WE

## 30MOS 1 WAY / 2 WAY MECHANISM - OUTSIDE



### Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Switch function	2-way
Actuator	Rocker
Number of rocker	1
Device mounting	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Outside
Marking location	Marking on surface

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	13.7 g
Package 1 Height	22 mm
Package 1 width	22 mm
Package 1 Length	30 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.078 kg
Package 2 Height	36 mm
Package 2 width	54 mm
Package 2 Length	74 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	8 kg
Package 3 Height	226 mm
Package 3 width	191 mm
Package 3 Length	359 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>