

Product data sheet

Characteristics

30PBBP-WE

Impress Series, Push Button Switch, 16A
Momentary Action, Bell Press Mechanism,
Series 30



Main

Range of product	Impress Series 30
Product or component type	Push-button
Colour	White electric
Product brand	Clipsal
Device presentation	Basic element





Complementary

Colour code	WE
Actuator	Push-button
Local signalling	Without light indicator
Material	Plastic
[Ue] rated operational voltage	250 V AC
Inrush current	16 A
Depth	10 mm
Width	21 mm
Length	21 mm
Load type	Fluorescent lamp 16 AX LEDi lamp 250 W

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	2.9 cm
Package 1 Length	6.6 cm
Package 1 Weight	22.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

 [End Of Life Information](#)
