

Product data sheet

Characteristics

30RJ45SM6AF

SOCKET MODULE CAT6A FTP RJ45



Main

Product brand	Clipsal
Range of product	Titanium
Product or component type	Modular jack

Complementary

Connector type	RJ45
Communication network category	6A
AWG gauge	AWG 24...AWG 22
[In] rated current	2 A
Material	Phosphor bronze
Depth	41 mm
Width	23 mm
Height	26 mm

Packing Units

Package 1 Weight	38.900 g
Package 1 Height	30.000 mm
Package 1 width	80.000 mm
Package 1 Length	60.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.