

Product data sheet

Characteristics

30RJ45SMA6A-WE

SOCKET MODULE CAT6A RJ45



Main

Colour	White electric
Product brand	Clipsal
Range of product	Actassi
Product or component type	Modular jack

Complementary

Colour code	WE
Connector type	110 RJ45
Communication network category	6 _A
Fixing mode	Special tool
AWG gauge	AWG 24...AWG 22
[In] rated current	1.5 A
Material	Phosphor bronze
Depth	35 mm
Width	23 mm
Height	23 mm

Packing Units

Package 1 Weight	0.015 kg
Package 1 Height	35.000 mm
Package 1 width	23.000 mm
Package 1 Length	23.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile