

# Product data sheet

## Characteristics

# 30RJ64SM-WE

## SOCKET MOD 6W/4C MECH



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Actassi
Product or component type	Socket-outlet

### Complementary

Colour code	WE
Number of ways	6 ways
Connector type	110 RJ11
Communication network category	3
Fixing mode	Special tool
AWG gauge	AWG 26...AWG 22

### Packing Units

Package 1 Weight	8.1 g
Package 2 Weight	0.11 kg
Package 3 Weight	3.85 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.