

Product data sheet

Characteristics

30RJ66SM-WE

SOCKET MOD 6W/6C MECH



Main

| | |
|---------------------------|----------------|
| Colour | White electric |
| Product brand | Clipsal |
| Range of product | Actassi |
| Product or component type | Socket-outlet |

Complementary

| | |
|--------------------------------|-----------------|
| Colour code | WE |
| Number of ways | 6 ways |
| Connector type | 110 RJ12 |
| Communication network category | 3 |
| Fixing mode | Special tool |
| AWG gauge | AWG 26...AWG 22 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 8 g |
| Package 1 Height | 30 mm |
| Package 1 width | 25 mm |
| Package 1 Length | 25 mm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 0.11 kg |
| Package 2 Height | 39 mm |
| Package 2 width | 55 mm |
| Package 2 Length | 115 mm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 350 |
| Package 3 Weight | 3.85 kg |
| Package 3 Height | 170 mm |
| Package 3 width | 282 mm |
| Package 3 Length | 300 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |