

Product data sheet

Characteristics

30RJ66SMT-WE

Clipsal Actassi, Modular Socket, Category 3, 6 Way, 6 Contact Socket Mechanism, Telephone



Main

Colour	White electric
Product brand	Clipsal
Range of product	Actassi
Product or component type	Socket-outlet

Complementary

Colour code	WE
Number of ways	6 ways
Connector type	110 RJ12
Communication network category	3
Fixing mode	Special tool
AWG gauge	AWG 26...AWG 22

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	2.7 cm
Package 1 Length	2.7 cm
Package 1 Weight	8 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.2 cm
Package 2 Width	5.6 cm
Package 2 Length	11.8 cm
Package 2 Weight	108 g
Unit Type of Package 3	CAR
Number of Units in Package 3	350
Package 3 Height	17 cm
Package 3 Width	28.2 cm
Package 3 Length	30 cm
Package 3 Weight	3.85 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile