

Product data sheet

Characteristics

30RJ88SMA5-CM

Clipsal Actassi, Socket Module, 8W/8C Mechanism



Main

Colour	Cream
Product brand	Clipsal
Range of product	Titanium
Product or component type	Modular jack

Complementary

Colour code	CM
Number of ways	8 ways
Connector type	110 RJ45
Communication network category	5e
Fixing mode	Special tool
AWG gauge	AWG 24...AWG 22
[In] rated current	1.5 A
Material	Phosphor bronze

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.016 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.