

Product data sheet

Characteristics

30RSM3-KB-WE

KNOB TO SUIT 30RSM3 - WE



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Number of rocker	1
Device mounting	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	15 A
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.5 g
Package 1 Height	1.1 cm
Package 1 width	1.6 cm
Package 1 Length	1.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	18.0 g
Package 2 Height	3.6 cm
Package 2 width	5 cm
Package 2 Length	7.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	500.0 kg
Package 3 Height	22.6 cm
Package 3 width	19.1 cm
Package 3 Length	35.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile