

## Product data sheet

### Characteristics

# 30RSM3-WE

## Switch Mechanism, 30 Series, 250V 15A - Rotary 3 On - 1 Off



### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element

### Complementary

Control type	Rotary knob
Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	15 A
Marking	Without marking

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.2 cm
Package 1 Length	4.1 cm
Package 1 Weight	18 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations