

Product data sheet

Characteristics

30RUM-WE

SWITCH MECH 1/2W 10A RUMPUS



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	2-way
Number of rocker	1
Device mounting	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Rumpus
Marking location	Marking on surface
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	13.8 g
Package 1 Height	3 cm
Package 1 width	2.2 cm
Package 1 Length	2.2 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	10 kg
Package 2 Height	3.9 cm
Package 2 width	5.5 cm
Package 2 Length	11.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	500 kg
Package 3 Height	23.7 cm
Package 3 width	20.3 cm
Package 3 Length	30 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile