

Product data sheet

Characteristics

30STM-WE

Clipsal - Mechanisms, Mechanisms - Marked, STUDY, 30 Series, 10A



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element




Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Study
Marking location	Marking on surface
Mounting Type	Clip-in
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29 cm
Package 1 Width	23.85 cm
Package 1 Length	23.85 cm
Package 1 Weight	14 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

