

## Product data sheet

### Characteristics

# 30T-WE

## Standard Series, Flush Switch, 1 Gang, 1-Way/2-Way, 250VAC, 10A, Miniature Architrave



### Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate

### Complementary

Switch function	1-way 2-way
Number of rocker	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	11.4 cm
Package 1 Length	9.7 cm
Package 1 Weight	21 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9 cm
Package 2 Width	7.6 cm
Package 2 Length	17 cm
Package 2 Weight	0.262 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	23.8 cm
Package 3 Width	34.2 cm
Package 3 Length	39 cm
Package 3 Weight	7 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>