

## Product data sheet

### Characteristics

## 30USM-DB

Clipsal - Mechanisms, Universal Rocker Clipsal  
- Mechanisms, Switch, 1-Way/2-Way, 250VAC,  
20A



### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element

### Complementary

Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A 16 AX, fluorescent lamp
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	2-way 1-way

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	2.5 cm
Package 1 Length	3.0 cm
Package 1 Weight	14.1 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations