

Product data sheet

Characteristics

30USMOV-WE

SWITCH MECH 1/2W 20A 16AX OVEN.

30USMOV,CM REPLACES 30M20HW,SG.



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	2-way 1-way
Number of rocker	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A 16 AX, fluorescent lamp
Marking	Oven
Marking location	Marking on surface
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	14 g
Package 1 Height	2.7 cm
Package 1 Width	2.4 cm
Package 1 Length	2.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	5 kg
Package 2 Height	3.4 cm
Package 2 Width	5.2 cm
Package 2 Length	7.3 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	500 kg
Package 3 Height	22.6 cm
Package 3 Width	19.1 cm
Package 3 Length	35.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile