

## Product data sheet

### Characteristics

# 31/2VA-WE

## Flush Switch, Standard Series, 1 Gang, 250VAC, 10A, Large Format



### Main

Range of product	Standard Series
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

### Complementary

Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	2-way 1-way

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	11.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	87.8 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	12.6 cm
Package 2 Width	14.6 cm
Package 2 Length	15.4 cm
Package 2 Weight	0.522 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	30.2 cm
Package 3 Width	35 cm
Package 3 Length	35 cm
Package 3 Weight	6.1 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations