

Product data sheet

Characteristics

31/2VA-WE

SWITCH 1 GANG 10A 250V 115MM SQ



Main

Range of product	Standard Series
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	2-way 1-way
Number of rocker	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	87.8 g
Package 1 Height	2.8 cm
Package 1 width	11.6 cm
Package 1 Length	11.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.522 kg
Package 2 Height	12.6 cm
Package 2 width	14.6 cm
Package 2 Length	15.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	6.1 kg
Package 3 Height	30.2 cm
Package 3 width	35 cm
Package 3 Length	35 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile