

Product data sheet

Characteristics

3105RG6Q3R

CABLE RG6 QUADSHIELD 305M RL



Main

Product brand	Clipsal
Product or component type	Cable
Sheath type	Foil + braiding
Colour	External sheath: black

Complementary

Diameter	Conductor: inner: 1.02 mm Conductor: external: 4.57 mm
Material	Inside bare copper conductor Outside aluminium conductor
Cable stiffness	Solid class 1
Cable insulation material	PVC (polyvinyl chloride) PE (polyethylene)
External diameter	7.57 mm
AWG gauge	AWG 18

Environment

Ambient air temperature for operation	80 °C
---------------------------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	15.1 kg
Package 1 Height	0.294 mm
Package 1 width	0.36 mm
Package 1 Length	0.37 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile