


## Product data sheet

### Characteristics

# 3105SPF4

## SPLITTER 4-WAY F TERRESTIAL 1



### Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

### Complementary

Connections - terminals	F connection
Transmission frequency	5...1000 MHz
Maximum splitter loss	7.8 dB
Number of outputs	4
Number of inputs	1
Number of mounting holes	2

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	68 g
Package 1 Height	2.5 cm
Package 1 width	11 cm
Package 1 Length	12.5 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>