

Product data sheet

Characteristics

3105SPF6

SPLITTER 6-WAY F TERRESTIAL 1



Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

Complementary

Connections - terminals	F connection
Transmission frequency	5...1000 MHz
Maximum splitter loss	10.7 dB
Number of outputs	6
Number of inputs	1
Number of mounting holes	2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.14 kg
Package 1 Height	40 mm
Package 1 width	110 mm
Package 1 Length	165 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile