

Product data sheet

Characteristics

3105SPF8

Actassi Terrestrial Splitter, 8 Way, F-Type, Terrestrial, 1 Leg Power Pass, 1GHz



Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

Complementary

Connections - terminals	F connection
Transmission frequency	5...1000 MHz
Maximum splitter loss	11.8 dB
Number of outputs	8
Number of inputs	1
Number of mounting holes	2

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	11 cm
Package 1 Length	16 cm
Package 1 Weight	0.16 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes