

Product data sheet

Characteristics

3105SPF8

SPLITTER 8-WAY F TERRESTIAL 1



Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

Complementary

Connections - terminals	F connection
Transmission frequency	5...1000 MHz
Maximum splitter loss	11.8 dB
Number of outputs	8
Number of inputs	1
Number of mounting holes	2

Packing Units

Package 1 Weight	0.140 kg
Package 1 Height	40.000 mm
Package 1 width	110.000 mm
Package 1 Length	160.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.