

Product data sheet

Characteristics

3105SPFP2

SPLITTER 2-WAY F-TYPE(2GHZ) PO



Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

Complementary

Connections - terminals	F connection
Transmission frequency	5...2400 MHz
Maximum splitter loss	6.3 dB
Number of outputs	2
Number of mounting holes	2

Environment

Standards	Foxtel F10082/C Austar A01564
-----------	----------------------------------

Packing Units

Package 1 Weight	0.080 kg
Package 1 Height	20.000 mm
Package 1 width	110.000 mm
Package 1 Length	125.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------