

Product data sheet

Characteristics

3105SPFP2

SPLITTER 2-WAY F-TYPE(2GHZ) PO



Main

| | |
|---------------------------|---------------------|
| Product brand | Clipsal |
| Range of product | Electricimagination |
| Product or component type | Splitter block |
| Number of terminals | 1 earth contact |

Complementary

| | |
|--------------------------|--------------|
| Connections - terminals | F connection |
| Transmission frequency | 5...2400 MHz |
| Maximum splitter loss | 6.3 dB |
| Number of outputs | 2 |
| Number of mounting holes | 2 |

Environment

| | |
|-----------|----------------------------------|
| Standards | Foxtel F10082/C Austar A01564 |
|-----------|----------------------------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.12 kg |
| Package 1 Height | 2 cm |
| Package 1 width | 11 cm |
| Package 1 Length | 12.5 cm |

Offer Sustainability

| | |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.