

## Product data sheet

### Characteristics

# 3105SPFP3

## Splitter, Clipsal Actassi, 3-Way F-Type(2Ghz) Po

### Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

### Complementary

Connections - terminals	F connection
Transmission frequency	5...2400 MHz
Maximum splitter loss	11.5 dB
Number of outputs	3
Number of mounting holes	2

### Environment

Standards	Foxtel F10082/C
-----------	-----------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	10.6 cm
Package 1 Length	7.6 cm
Package 1 Weight	0.1 kg

### Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.