

Product data sheet

Characteristics

3105SPFP3

SPLITTER 3-WAY F-TYPE(2GHZ) PO



Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

Complementary

Connections - terminals	F connection
Transmission frequency	5...2400 MHz
Maximum splitter loss	11.5 dB
Number of outputs	3
Number of mounting holes	2

Environment

Standards	Foxtel F10082/C
-----------	-----------------

Packing Units

Package 1 Weight	0.100 kg
Package 1 Height	16.000 mm
Package 1 width	106.000 mm
Package 1 Length	76.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------