

## Product data sheet

### Characteristics

# 3105SPFP4

## Clipsal Actassi, Splitter 4-Way F-Type(2Ghz) Po



### Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

### Complementary

Connections - terminals	F connection
Transmission frequency	5...2400 MHz
Maximum splitter loss	11.5 dB
Number of outputs	4
Number of mounting holes	2

### Environment

Standards	Foxtel F10082/C Austar A01592
-----------	----------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.1 kg

### Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations