

Product data sheet

Characteristics

3105SPFP4

Clipsal Actassi, Splitter 4-Way F-Type(2Ghz) Po



Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact

Complementary

Connections - terminals	F connection
Transmission frequency	5...2400 MHz
Maximum splitter loss	11.5 dB
Number of outputs	4
Number of mounting holes	2

Environment

Standards	Foxtel F10082/C Austar A01592
-----------	----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.1 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------