

Product data sheet

Characteristics

3106W06C604-GY

Actassi - cabinet - wall mounted - 6U - 363x600x400 mm



Main

Range	Actassi
Product or component type	Cabinet
Device application	Installation
Type of front cover	Glazed door
Door type	Glazed door - with key lock - front
Accessibility for operation	Front
Colour tint	Grey (RAL 7035)

Complementary

Product compatibility	Standard 19" rack
Number of rack unit	6U
Device mounting	Wall mounted
Material	Steel
Surface finish	Powder coated
Thickness	1.2 mm
Maximum load	40 kg
Height	363 mm
Width	600 mm
Depth	400 mm

Packing Units

Package 1 Weight	7000.000 g
Package 1 Height	330.000 mm
Package 1 width	600.000 mm
Package 1 Length	400.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------