

Product data sheet

Characteristics

3106W06C604-GY

Wall Cabinet, Clipsal Actassi, 19 Inch 6RU 600W x 400D



Main

Range	Actassi
Product or component type	Cabinet
Device application	Installation
Type of front cover	Glazed door
Door type	Glazed door - with key lock - front
Accessibility for operation	Front
Colour tint	Grey (RAL 7035)

Complementary

Product compatibility	Standard 19" rack
Number of rack unit	6U
Device mounting	Wall mounted
Material	Steel
Surface finish	Powder coated
Thickness	1.2 mm
Maximum load	40 kg
Height	363 mm
Width	600 mm
Depth	400 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	60 cm
Package 1 Length	40 cm
Package 1 Weight	8500 g
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Height	150 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	51000 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.