

## Product data sheet

### Characteristics

# 3106W06C605-GY

## Actassi - cabinet - wall mounted - 6U - 363x600x500 mm



### Main

Range	Actassi
Product or component type	Cabinet
Device application	Installation
Type of front cover	Glazed door
Door type	Glazed door - with key lock - front
Accessibility for operation	Front
Colour tint	Grey (RAL 7035)

### Complementary

Product compatibility	Standard 19" rack
Number of rack unit	6U
Device mounting	Wall mounted
Material	Steel
Surface finish	Powder coated
Thickness	1.2 mm
Maximum load	40 kg
Height	363 mm
Width	600 mm
Depth	500 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33.0 cm
Package 1 Width	60.0 cm
Package 1 Length	50.0 cm
Package 1 Weight	10500.0 g

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------