

Product data sheet

Characteristics

3106WS12C605-GY

Actassi - cabinet - wall mounted - 12U - swing frame - 630x600x500 mm



Main

Range	Actassi
Product or component type	Cabinet
Device application	Installation
Type of front cover	Glazed door
Door type	Glazed door - with key lock - front
Accessibility for operation	Front body and front rear
Colour tint	Grey (RAL 7035)

Complementary

Product compatibility	Standard 19" rack
Number of rack unit	12U
Device mounting	Wall mounted
Material	Steel
Surface finish	Powder coated
Thickness	1.2 mm
Maximum load	20 kg
Height	630 mm
Width	600 mm
Depth	500 mm

Packing Units

Package 1 Weight	16000.000 g
Package 1 Height	590.000 mm
Package 1 width	600.000 mm
Package 1 Length	600.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------