

Product data sheet

Characteristics

3106WS18C605-GY

Actassi - cabinet - wall mounted - 18U - swing frame - 897x600x500 mm



Main

Range	Actassi
Product or component type	Cabinet
Device application	Installation
Type of front cover	Glazed door
Door type	Glazed door - with key lock - front
Accessibility for operation	Front body and front rear
Colour tint	Grey (RAL 7035)

Complementary

Product compatibility	Standard 19" rack
Number of rack unit	18U
Device mounting	Wall mounted
Material	Steel
Surface finish	Powder coated
Thickness	1.2 mm
Maximum load	20 kg
Height	897 mm
Width	600 mm
Depth	500 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	86 cm
Package 1 Width	60 cm
Package 1 Length	60 cm
Package 1 Weight	26500 g
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	150 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	53000 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------