

## Product data sheet

### Characteristics

# 3110L64/3

## LEAD TELE RJ12 6P4C 3M IVY



### Main

Product brand	Clipsal
Colour	External sheath: ivory

### Complementary

Termination 1	Plug
Termination 2	Plug
Connector type	4 2 - 6 ways RJ12
Length	3 m

### Packing Units

Package 1 Weight	0.082 kg
Package 1 Height	30.000 mm
Package 1 width	101.000 mm
Package 1 Length	205.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.