

## Product data sheet

### Characteristics

# 319N-WE

## Timer 319 Series - Pneumatic - Neon indicator - 250 V - 6 AX - White Electric



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Series 319
Device presentation	Basic element with full cover plate

### Complementary

Colour code	WE
Device mounting	Flush
Material	Plastic
Surface finish	Glossy
Autonomy	0.0083...0.33 h
[Ue] rated operational voltage	250 V
Network frequency	50/60 Hz
Rated current	6 A

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	158 g
Package 1 Height	71 mm
Package 1 width	91 mm
Package 1 Length	117 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.91 kg
Package 2 Height	10.2 cm
Package 2 width	12.6 cm
Package 2 Length	36.6 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	8 kg
Package 3 Height	36 cm
Package 3 width	34.5 cm
Package 3 Length	40.5 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>