

Product data sheet

Characteristics

31BLA-WE

SWITCH 1 GANG 10A 250V INTERMEDIATE



Main

| | |
|---------------------|-------------------------------------|
| Range of product | Standard Series |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |

Complementary

| | |
|--------------------------------|-----------------|
| Switch function | 1-way 2-way |
| Number of rocker | 1 |
| Device mounting | Flush |
| Fixing mode | By screws |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 10 A |
| Marking | Without marking |
| Actuator | Rocker |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.4 cm |
| Package 1 Width | 5.5 cm |
| Package 1 Length | 10.6 cm |
| Package 1 Weight | 44 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 85 cm |
| Package 2 Width | 97 cm |
| Package 2 Length | 150 cm |
| Package 2 Weight | 450 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 100 |
| Package 3 Height | 237 cm |
| Package 3 Width | 203 cm |
| Package 3 Length | 300 cm |
| Package 3 Weight | 4.5 kg |

Offer Sustainability

| | |
|----------------------------|-----------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |